

SGG MASTER-SOFT®
Source of light and softness

SGG MASTERGLASS


Architectural patterned glass

SAINT-GOBAIN GLASS DESIGN

The future of habitat. Since 1665

# SGG MASTER-SOFT®

### Source of light and softness



#### **Applications**

Light screen, internal structure, furniture, sgg MASTER-SOFT is all at the same time. Its structure is an ideal place for the interplay of light and its contrasts. It is ideal for use in the home, offices, shops, hotels and restaurants.

#### Its applications are limitless:

Furniture, partitions, shower screens, doors, windows, etc.

2 ● sgg MASTER-SOFT



## reddot award 2015 best of the best

sgg MASTER-SOFT has just been awarded a **Red Dot award "Best of the Best"**, a very high distinction awarded for the best international design.

sgg MASTER-SOFT is a tactile material which catches the eye and is pleasing to the touch. The glass has a soft texture with a

quilted pattern and a fine-grained touch. It conveys a background blur, becoming blurred as the body moves away.





#### Description

sgg MASTERGLASS is a patterned glass which complies with the requirements of standard EN 572-5.

As with all other products in the sgg MASTERGLASS range, the texture of sgg MASTER-SOFT is obtained by casting and rolling the glass between two engraved cylinders. This extremely precise operation enables the glass to be finely engraved. The glass has one textured face and one smooth face.

#### Processing

sgg MASTERGLASS glass is suitable for numerous types of processing.

#### It can be:

curved or edgeworked to enhance the impact of its appearance; toughened or laminated for safety purposes; lacquered (on the smooth face); incorporated in enhanced thermal insulation double-glazed units for comfort.

#### Installation

sgg MASTERGLASS must be installed in accordance with current standards and regulations.

As with all textured glass, the pattern on sgg MASTERGLASS runs in one direction. To obtain a uniform appearance, the cut sheets must be placed side by side with the pattern on the glass running in the same direction. Special care must be taken cutting the glass when continuity of the pattern is required.



3 • SAINT-GOBAIN GLASS DESIGN

#### THE 6 OTHER SGG MASTERGLASS MODELS ARE:





SGG MASTER-RAY



SGG MASTER-LENS



SGG MASTER-POINT



sgg MASTER-LIGNE




SGG MASTER-SHINE

### SGG MASTERGLASS range The sGG MASTERGLASS range consists of seven models.

Dimensions	3 210 x 2 000		3 300 x 2 040	
Thickness (mm)	4	6	8	10
see MASTER-SOFT	•		•	
sgg MASTER-CARRE	•	•	•	•
sgg MASTER-LENS	•	•	•	
sgg MASTER-LIGNE	•	•	•	
sgg MASTER-POINT	•	•	•	
sgg MASTER-RAY	•	•	•	
sgg MASTER-SHINE	•	•	•	

#### **Tolerance on thicknesses:**

4 and 6 mm:  $\pm$  0.5 mm / 8 mm:  $\pm$  0.8 mm / 10 mm:  $\pm$  1.0 mm





Saint-Gobain Glass France 18 av d'Alsace 92400 Courbevoie

N° Indigo 0 820 810 820

www.saint-gobain-glass.com glassinfo.fr@saint-gobain.com